



P.C.B LAYOUT
TOLERANCE: ±0.05



Ordering Information:

A2541WV-XP - *** - * - * - ***
1 2 3 4 5

1.Part No.

2.Size(H):

(blank): 2.54mm

H15: 1.50mm

H17: 1.70mm

H20: 2.00mm

H30: 3.00mm

3.Style:

(blank): Type 1

K: Type 2

4.Material:

(blank): PBT,UL94V-0

GN: PBT,UL94V-0 (Green)

NAT: PBT,UL94V-0 (Natural)

6T: Nylon 6T,UL94V-0

GWT: Nylon 6T,UL94V-0,GWT 750°C

5.Finish:


(blank): Gold over Nickel

G10: Gold over Nickel(Au:10u")

G15: Gold over Nickel(Au:15u")

G30: Gold over Nickel(Au:30u")

T: Tin over Nickel



SPECIFICATIONS:

Current Rating: 3A AC,DC

Voltage Rating: 250V AC,DC

Temperature Range: -40°C ~ +105°C

Contact Resistance: 20mΩ Max

Insulation Resistance: 1000MΩ Min


Withstanding Voltage: 1500V AC/minute

Pin Material: Brass/Gold over Nickel

Material: PBT,UL94V-0 (Black)

Ordering Information & Dimensions

Circuits	Dimensions (mm)		Circuits	Dimensions (mm)		Circuits	Dimensions (mm)	
	A	B		A	B		A	B
1P	---	2.54	15P	35.56	38.10	29P	71.12	73.66
2P	2.54	5.08	16P	38.10	40.64	30P	73.66	76.20
3P	5.08	7.62	17P	40.64	43.18	31P	76.20	78.74
4P	7.62	10.16	18P	43.18	45.72	32P	78.74	81.28
5P	10.16	12.70	19P	45.72	48.26	33P	81.28	83.82
6P	12.70	15.24	20P	48.26	50.80	34P	83.82	86.36
7P	15.24	17.78	21P	50.80	53.34	35P	86.36	88.90
8P	17.78	20.32	22P	53.34	55.88	36P	88.90	91.44
9P	20.32	22.86	23P	55.88	58.42	37P	91.44	93.98
10P	22.86	25.40	24P	58.42	60.96	38P	93.98	96.52
11P	25.40	27.94	25P	60.96	63.50	39P	96.52	99.06
12P	27.94	30.48	26P	63.50	66.04	40P	99.06	101.60
13P	30.48	33.02	27P	66.04	68.58			
14P	33.02	35.56	28P	68.58	71.12			



TYPE 1

TYPE 2

CJTconn

CHANGJIANG CONNECTORS CO.,LTD.

Unit: mm, Scale: 5:1, Sheet: 1 of 1

DRWN: Dengchun Yi, CHK'D: Dlankul Wan, APPR: Jack Yin

General Tolerances: x.xx±0.25, x.xxx±0.20, x.xxxx±0.15, ANGLES ±1°, THIRD ANGLE PROJECTION

TITLE: 2.54mm PLTCH 180° SINGLE ROW PIN HEADER

DRAWING NO.: A2541WV-XP, REV A4

REV	DESCRIPTION	DATE
A4	CHANGE THE DRAWING	2020.09.02
A3	CHANGE THE DRAWING	2020.01.13
A2	CHANGE THE INFORMATION	2019.04.29
A1	UPDATED VERSION	2018.03.30
A0	NEW RELEASE	2009.05.10