

MATERIAL: NYLON 6/6 UL 94 V-2 (RMS-01) COLOR: NATURAL PART NUMBER	MATERIAL: NYLON 6/6 UL 94 V-2 UVB (RMS-46) COLOR: BLACK PART NUMBER	MIN LOOP TENSILE STRENGTH lbs [N]	LENGTH REF.	MAX BUNDLE DIAMETER	"W" REF WIDTH	"T" REF THICKNESS	
WITA-18SF	WITA-18SF-UVB	18 [80]	3.85 [97.8]	.87 [22]	.098 [2.5]	.039 [1]	
WITA-18R	WITA-18R-UVB		4.72 [120]	1.06 [26.9]		.044 [1.1]	
WITA-18L	WITA-18L-UVB		5.91 [150]	1.46 [37.1]		.039 [1]	
WITA-18V	WITA-18V-UVB		7.87 [200]	2.13 [54.1]		.047 [1.2]	
WITA-18X	WITA-18X-UVB		15.75 [400]	4.56 [116]			
WITA-40R	WITA-40R-UVB	40 [180]	5.91 [150]	1.48 [37.6]	.14 [3.6]	.051 [1.3]	
WITA-40L	WITA-40L-UVB		7.87 [200]	2.05 [52]			
WITA-40XL	WITA-40XL-UVB		8.07 [205]	2.10 [53.3]			
WITA-40VL	WITA-40VL-UVB		11.81 [300]	3.27 [83]		.055 [1.4]	
WITA-50S	WITA-50S-UVB	50 [222]	6.30 [160]	1.52 [38.7]	.18 [4.6]	.052 [1.3]	
WITA-50R	WITA-50R-UVB		7.90 [200.7]	1.95 [49.5]		.047 [1.2]	
WITA-50RL	WITA-50RL-UVB		11.02 [280]	3.03 [77]			
WITA-50L	WITA-50L-UVB		15.75 [400]	4.52 [114.8]		.18 [4.6]	.052 [1.3]
WITA-50XL	WITA-50XL-UVB		25.00 [635]	7.48 [190]		.19 [4.8]	
WITA-120S	WITA-120S-UVB	120 [534]	8.60 [218]	2.01 [51]	.30 [7.6]		
WITA-120R	WITA-120R-UVB		15.75 [400]	4.45 [113]			.063 [1.6]
WITA-120L	WITA-120L-UVB		21.65 [550]	6.38 [162]			
WITA-175R	WITA-175R-UVB	175 [778]	24.00 [610]	7.02 [178]	.35 [9]		
WITA-175L	WITA-175L-UVB		36.00 [914.4]	10.91 [277]			.071 [1.8]

NOTES:

1. MATERIAL OPTIONS:

NYLON 6/6 UL94 V-0 (RMS-19)  
 COLOR: NATURAL.  
 ONLY AVAILABLE FOR WITA-18R AND WITA-50R.  
 TO ORDER ADD "-V0" TO THE END OF PART NUMBER


NYLON 6/6 UL94 V-2 HEAT STABILIZED (RMS-47)  
 COLOR: BLACK.  
 AVAILABLE AS STANDARD FOR WITA-18R, WITA-40R, WITA-50R, WITA-50RL,  
 ALL OTHER PARTS ARE AVAILABLE BY SPECIAL ORDER ONLY.  
 TO ORDER ADD "-HS" TO THE END OF PART NUMBER

2. OTHER COLORS: AVAILABLE BY SPECIAL ORDER.

3. PACKAGING QUANTITIES ARE REFLECTED AS THE SUFFIX "-LETTER".

EXAMPLE: WIT-50R-M."-M" FOR 1000 PCS PER BAG

- Q = 25 pcs
- L = 50 pcs
- C = 100 pcs
- D = 500 pcs
- M = 1000 pcs



REV.	DESCRIPTION	ENGR.	DATE
D	UPDATED PART NUMBERS AND MATERIAL , SEE CO 1365 FOR CHANGES	DZ	07/17/2012
C	ADDED NOTE 5. , SEE CO 200661 FOR CHANGES	DK	05/12/2011
B	UPDATED NOTE ON V-0 MATERIAL, SEE CO 200555 FOR CHANGES	DK	07/12/2010
A	RELEASED FOR PRODUCTION, CO 200524	DK	05/27/2010

TITLE: <b>WRAP IT TIES</b>				UNITS IN [MM]		FINAL	
CREATED USING SOLIDWORKS	FILE #: WIT(A)-XX	DWN: D.K.	APP: D.K.	PART #			
TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC.=±1/64 ANG.=±1°	SHEET: 1 OF 1   SHEET SIZE: B	DT: 04/22/10	CHKD: D.Z.	<b>SEE TABLE</b>		PRINT TYPE	
RE: RICHCO, INC.		RICHCO, INC. WWW.RICHCO-INC.COM				<b>CA</b>	