






poles	A	B
2P	2.5	7.5
3P	5.0	10.0
4P	7.5	12.5
5P	10.0	15.0
6P	12.5	17.5
7P	15.0	20.0
8P	17.5	22.5
9P	20.0	25.0
10P	22.5	27.5
11P	25.0	30.0
12P	27.5	32.5
13P	30.0	35.0
14P	32.5	37.5
15P	35.0	40.0



技术参数 (SPECIFICATIONS)

- 额定电压: 250V AC DC
- Voltage rating: 250V AC DC
- 额定电流: 3.0A AC DC #22
- Current rating: 3.0A AC DC #22
- 耐压值: 1000V AC/minute
- Withstand voltage: 1000V AC/minute
- 绝缘电阻: 1000MΩ MIN
- Insulation resistance: 1000MΩ MIN
- 接触电阻: 0.02Ω MAX
- Contact resistance: 0.02Ω MAX
- 工作温度: -25℃ ~ +85℃
- Working Temperature: -25℃ ~ +85℃
- 间距: 2.5mm
- Pitch: 2.5mm
- 材料 (MATERIAL)
- 外壳: 尼龙66
- Housing: PA66
- 插针: 黄铜
- Pin: Brass

APPROVALS		DATE	TITLE:				
DRAWN	ZHIWEI, CHEN	2015.07.07	GP01-2501W-NP				
CHECKED							
APPROVALS							
TOLERANCES ARE		30~0.15	±0.30	ANGLE			
		10~0.10	±0.20	UNIT: mm			
		5~0.10	±0.15	SCALE: 1:1			
		~ 5	±2°	PROJ.			
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	SHEET 1 OF 1
	A		NEW				

PCB LAYOUT

**GEPU 歌普**