


REVISION	DESCRIPTION	DATE	DRAFTER
A0	FIRST RELEASE	19.07.24	Mark



- 技术要求:
- 1 电气特性: 特性阻抗:50Ω; 适用频率范围:DC-6GHz, VSWR<2.0;
 - 2 断短路与高压测试: 100%使用线材综合测试仪测试。
 - 3 尺寸检验: [*]为FAI检测项目; *为重点检测项目; ■为CPK管制项目。
 - 4 外观检验: 目视全检。产品表面不得有刮伤、破损和脏污; 镀层色泽光亮均匀, 不得有氧化。
 - 5 包装规范: 25 PCS/扎, 4扎/包。
 - 6 环保要求: 产品及其使用之物料皆需要符合RoHS要求。

No.	PART NUMBER	PART NAME & DESCRIPTION	Q' TY	REMARKS
8	2TA035BK1-015	OD:3.5*L15.0mm, 无卤阻燃, 125H2普通型, 黑色	2	---
7	2LC15S-601	铜管, C3602铜料, 镀镍OD:3.9*L9.0*内孔3.2mm	2	---
6	2LC15PM621-7	SMA 公头侧盖镀金, M5*Txxmm	1	---
5	2LC15PM621-6	绝缘粒, 材质TPFE, OD3.8*Txxmm	1	---
4	2LC15PM621-2	90度SMA公头公针H8.0*L17.0*W13.0镀金	1	(主体+胶芯)
3	2LC15PM623-5	SMA 公针OD:1.5*L8.3mm 镀金	1	---
2	2LC15PM623-2	SMA公头 H8.0*L16.5镀金	1	(主体+胶芯)
1	2C5R31613BN1	RG316透明棕双银线-50 OHM	1	---

GENERAL TOLERANCE: LINEAR: X ±0.50 X.X ±0.30 X.XX ±0.10 X.XXX ±0.05 ANGLE: X° ±4.00° X.X° ±3.00° X.XX° ±2.00° X.XXX° ±1.00°		HJ-Tech 东莞市皇捷通讯科技有限公司 手机: 15015262131/13714786106	
FILE NAME: ENG/DATE: CHE/DATE:	产品图 Mark/19.07.24	TITLE: 射频频天线连接器组件 RF CABLE, RG316线, P1端SMA公头公针, P2端90度SMA公头公针, 外露线长L=150mm	P/N: HJ-316-SMA-L150mm
APP/DATE:	UNIT: mm	SCALE: 1:1	REVISION: A0
COMPLIANCE WITH THE REQUIREMENT: ■RoHS; □HF; □SONY SS-00259; □OTHERS		SHEET: 1/1	

COMPLIANCE WITH THE REQUIREMENT: ■RoHS; □HF; □SONY SS-00259; □OTHERS
*NO USING ESTRICTED AND BANNED SUBSTANCE

H384