


NOTES:
SPECIFICATION:

1. CURRENT RATING: 5.0A MAX
2. VOLTAGE: 100 VAC
3. TEMPERATURE RANGE: -30 °C ~ 85 °C
4. CONTACT RESISTANCE: 40 MILLIONHM MAX
5. INSULATION RESISTANCE: 100 MEGOHMS MIN.
6. INSERTION FORCE : 5N~20N
7. UNMATING FORCE: 8N~20N
8. DURABILITY: 10,000 CYCLES



USB3. 1 (TYPE/C) 母座

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
④	Shielding Plate	—	1	STAINLESS STEEL	—	—
③	Shell	—	1	STAINLESS STEEL	Ni Plated	—
②	Contact	—	24	COPPER ALLOY	Au/Ni Plated	—
①	Housing	—	1	LCP	Black	—

APPROVALS		DATE		HRO 宏 ELECTRONICS CO.,LTD		
DRAWN	JKN.LU	2014.5.29		TITLE:	USB CONNECTOR	
CHECKED				PART NO.	TYPE-C-31-M-04	
APPROVALS				UNIT: mm	SCALE: 1:1	PROJ:
TOLERANCES ARE	30~以上 ±0.30	10~30 ±0.25	ANGLE	DRAWING NO.		SHEET 1 OF 1
	5~10 ±0.20	~ 5 ±0.15	±2'			

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			