


Circuit Diagram



PCB Layout (Pattern Side)

- Typical Specifications :
1. Rating : DC 12V 50mA
  2. Travel:0.15±0.05mm
  3. Operating force:  
100gf,180gf,250gf
  4. Life:100,000 Cycles Min.

NO.1	
PART NO.	vigor
2	100±30
3	180±30
4	250±30

NO.2	
PART NO	MATERIAL/QTY
S	SUS/1PC
D	SUS/2PCS

NO.3-NO.4	
PART NO	NOTE
01~99	SERIAL NUMBER

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
④	Dust cover	---	1	KAPTON FILM	Yellow	---
③	Terminal	---	2	Phosphor Bronze	Plating silver	---
②	Contact	---	2	F.Ag/SUS	Plating silver	---
①	Base	---	1	Nylon	Black	---

APPROVALS		DATE
DRAWN	QIFENG:XU	2014/9/13

APPROVALS		TITLE:	PART NO.	SCALE:	PROJ.
CHECKED		TACT SWITCHS	K2-1827SR-AD0W-00	1:1	PROJ. 1
APPROVALS					
TOLERANCES ARE					
30~12.5	±0.30	ANGLE			
10~30	±0.20				
5~10	±0.15				
~5	±0.10				

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			



ELECTRONICS CO.,LTD

TACT SWITCHS

PART NO. K2-1827SR-AD0W-00

SCALE: 1:1

DRAWING NO. SHEET 1 OF 1