



PCB Layout(Pattern side)

Circuit Diagram



Note:
Operating force: 200±50gf

⑤	Contact Spring	—	1	Beryllium copper	Ag Plated	—
④	Terminal	—	4	Brass Strip	Ag Plated	—
③	Base	—	1	LCP	Black	—
②	Cover	—	1	SUS	Natural	—
①	Knob	—	1	NYLON	White	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE
DRAWN	J.X.Zhang	2013/9/27
 ELECTRONICS CO.,LTD		
CHECKED		
TITLE: TOGGLE SWITCHES		
APPROVALS		
PART NO. K3-1386S-F1		
TOGGLE SWITCHES		

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.																
	A		NEW																			
TOLERANCES ARE: <table border="1" style="display: inline-table; margin-left: 10px;"> <tr> <td>30~以上</td> <td>±0.30</td> <td>ANGLE</td> <td>±2°</td> </tr> <tr> <td>10~30</td> <td>±0.20</td> <td>UNIT: mm</td> <td></td> </tr> <tr> <td>5~10</td> <td>±0.15</td> <td>SCALE: 1:1</td> <td></td> </tr> <tr> <td>~5</td> <td>±0.10</td> <td>DRAWING NO.</td> <td></td> </tr> </table>							30~以上	±0.30	ANGLE	±2°	10~30	±0.20	UNIT: mm		5~10	±0.15	SCALE: 1:1		~5	±0.10	DRAWING NO.	
30~以上	±0.30	ANGLE	±2°																			
10~30	±0.20	UNIT: mm																				
5~10	±0.15	SCALE: 1:1																				
~5	±0.10	DRAWING NO.																				
SHEET 1 OF 1																						