



Circuit Diagram

NOTE:
 Rating: DC 12V 50mA
 Operating Force: 30±10gf
 Lifetime: 100,000 Cycles

PART NO.
K5-1620UA-01
K5-1620UN-01

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑤	Contact Spring	—	1	Phosphor Bronze	Ag Plated	—
④	Terminal	—	4	Phosphor Bronze	Ag Plated	—
③	Base	—	1	PA46	Black	—
②	Cover	—	1	SUS	Natural	—
①	Slider	—	1	PA46	Black	—

APPROVALS		DATE	HROELECTRONICS CO.,LTD				
DRAWN	J.X.Zhang	2013/8/28	ELECTRONICS CO.,LTD				
CHECKED			TITLE: DETECTOR SWITCHES				
APPROVALS			PART NO.				
TOLERANCES ARE		30~以上 ±0.30	10~30 ±0.20	ANGLE	UNIT: mm	SCALE: 1:1	PROJ:
		5~10 ±0.15	~ 5 ±0.10	±2'	DRAWING NO.		SHEET 1 OF 1

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
—	A	—	NEW	—	—	—