



**Specification:**

- Contact Resistance: 30m Ohm Max.
- Insulation Resistance: 1000M Ohm Min. At 500VDC.
- Rated Voltage And Current: 1.5A At 250VAC Minimum.
- Dielectric Withstanding Voltage:  
750V AC (rms) for 1 Minute(Rev. 1.1)
- Durability (Life Test): 1500 Cycles
- Insertion Force: 35 Newton Maximum.
- Extraction Force: 10 Newton Minimum.

RECOMMENDED P.C.B. LAYOUT

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING
③	Base	—	1	PA9T	White/black
②	Terminal	—	4	Phosphor Bronze	Ag Plated
①	Housing	—	1	BRASS	Ni Plated

APPROVALS	DATE	TITLE:
DRAWN	JIANKUN.LIU	2018.08.01
		ELECTRONICS CO.,LTD
		USB CONNECTOR

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			
TOLERANCES ARE 30~Ø±. ±0.30 ANGLE PART NO. U-B-M4SS-W-2 10~30 ±0.25 UNIT: mm SCALE: 1:1 PROJ: 5~10 ±0.20 ±2 DRAWING NO. SHEET 1 OF 1 ~5 ±0.15						