



PANEL THICKNESS	X
1.0	20
1.2	20
2.0	21
2.5	21

Rating :
 15A 250V AC UL cUL
 10A 250V AC 3C VDE KC

Insert And Extract Force: 1.36kgf~6.8kgf
 Terminal Strength: ≥80N
 Operating Life: ≥5000 cycles
 Withstand Voltage: Between all terminals:2000VAC (50-60Hz)1min
 terminals to Base:3750V AC (50-60Hz)1min
 Leakage Current : 1mA

Insulation Resistance: ≥100MΩ 500V DC
 Body Materil: NYLON 66 94V-0

SECTION:A-A

A4				普通公差	深圳市华灿天禄电子有限公司								
A3				COMMON TOLERANCE :									
A2				UP TO 5	±0.20	单位	mm	投影	⊕	品名	Ac Inlet C14型	比例	Free
A1				ABOVE 5 TO 30	±0.30	绘图	金泽松	核对	张彦龙	型号	DB-14		
REV.	DATE	REVISION DESCRIPTION	ISSUE	ANGULAR	±5°	日期	2021/8/4	核准	同培霄	料号	DB-14-2 F		