



PANEL CUT-OUT		
Z	Y	X
0.70~1.25	12.90~13.10	18.9~19.1
1.25~2.00	12.90~13.10	19.1~19.2
2.00~3.00	12.90~13.10	19.3~19.4

NOTES:

1. Rating:  
CQC 6A 250VAC 6(8)A 250VAC  
8A/128A 250VAC T105/55  
UL CUL 10GPA 125VAC  
6GPA 250VAC T105/55  
VDE ENEC 6(4)A 250VAC T85/55  
KC 6(4)A 250VAC T85/55
2. Circuit Diagram: 3P ON-ON
3. Terminal Strength:  $\geq 80N$
4. Electrical life:  $\geq 10000$  cycles
5. Withstand Voltage: Withstand Voltage: 1500VAC 1min  
Terminals to Button: 3000VAC 1min
6. Leakage Current: 1mA
7. Current resistance:  $\leq 50m\Omega$  (initial)
8. Insulation resistance:  $\geq 100M\Omega$
9. Body Material: NYLON 66 94V-2~0

SWITCHING CIRCUIT



普通公差:  
COMMON TOLERANCE:

UP TO 5	$\pm 0.20$
ABOVE 5 TO 30	$\pm 0.30$
ABOVE 30	$\pm 0.50$
ANGULAR	$\pm 5^\circ$

# 深圳市华灿天禄电子有限公司

单位 UNIT	mm	投影 PROJECTED	$\varnothing$	品名 PRODUCT NAME	跷板开关	比例 SCALE	Free
绘图 DRAWN BY	周金勇	核对 CHECKED BY	梁金勇	型号 MODEL NO.			RS601
日期 DATE	2015.10.15	核准 APPROVAL BY	周培雷	图号 DWG. NO.			RS601-1020011BB

A4		
A3		
A2		
A1		
REV.	DATE	REVISION DESCRIPTION