



| PANEL CUT-OUT | | |
|---------------|-------------|-----------|
| Z | Y | X |
| 0.70~1.25 | 22.10~22.20 | 30.1~30.2 |
| 1.25~2.00 | 22.10~22.20 | 30.3~30.4 |
| 2.00~3.00 | 22.10~22.20 | 30.4~30.5 |



- NOTES:
- Rating:
CCC 16(4)A 250V AC T105/55
VDE ENEC 16(4)A 250V AC T85/55
KC 16(4)A 250V AC T185/55
UL cUL 16GPA 125V AC/16GPA 250V AC T105/55
 - Circuit Diagram: 4P ON-OFF
 - Terminal Strength: $\geq 80N$
 - Electrical life: ≥ 10000 cycles
 - Withstand Voltage: Withstand Voltage: 1500VAC 1min
 - Terminals to Button: 3000VAC 1min
 - Leakage Current: 1mA
 - Current resistance: $\leq 50m\Omega$ (initial)
 - Insulation resistance: $\geq 100M\Omega$ 500V DC
 - Body Material: NYLON 66 94V-2~0

普通公差:
COMMON TOLERANCE:

| | |
|---------------|---------------|
| UP TO 5 | ± 0.20 |
| ABOVE 5 TO 30 | ± 0.30 |
| ABOVE 30 | ± 0.50 |
| ANGULAR | $\pm 5^\circ$ |

深圳市华灿天禄电子有限公司

| | | | | | | | |
|----------------|------------|-------------------|-----|--------------------|--------------------|-------------|------|
| 单位 UNIT | mm | 投影 PROJECTED | Φ | 品名 PRODUCT NAME | 跷板开关 | 比例 SCALE | Free |
| 绘图 DRAWN BY | 周金勇 | 核对 CHECKED BY | 梁金勇 | 型号 MODEL NO. | RS606 | | |
| 日期 DATE | 2016.01.07 | 核准 APPROVAL BY | 周培雷 | 图号 DWG NO. | RS606B-2011N012CRB | | |

| | | | |
|------|------|----------------------|-------|
| A4 | | | |
| A3 | | | |
| A2 | | | |
| A1 | | | |
| REV. | DATE | REVISION DESCRIPTION | ISSUE |