



PC Board Layout
Component Side Shown

NOTES:

MATERIAL :

- | | |
|--------------------|--|
| 1.HOUSING MATERIAL | : PBT UL94V-0 |
| 2.CONTACT MATERIAL | :PHOSPHOR BRONZE φ0.45mm. |
| 3.PLATING | :GOLD PLATING OVER NICKEL. |
| 4.SHIELD | :0.20mm THICKNESS COPPER ALLOY WITH NICKEL PLATED. |

ELECTRICAL:

- | | |
|--------------------------------------|------------------------------|
| 1.VOLTAGE RATING | :125 VAC RMS. |
| 2.CURRENT RATING | :15 AMP. |
| 3.CONTACT RESISTANCE | :30 MILLIOHMS MAX. |
| 4.INSULATION RESISTANCE | :500 MEGOHMS MIN @ 500V DC . |
| 5.DIELECTRIC WITHSTANDING RESISTANCE | :1000V AC RMS 50Hz. 1MIN. |

MECHANICAL:

- | | |
|----------------------------|------------------|
| 1.DURRABILITY | :750 CYCLES MIN. |
| 2.PCB RETENTION PRE-SOLDER | :1 LB MIN. |

ENVIRONMENTAL:

- | | |
|--------------|----------------|
| 1. STORAGE | : -40°C~+85°C |
| 2. OPERATION | : 0°C TO 70°C. |

ROHS2.0

本圖紙知識產權及版權由深圳市永丰盈电子有限公司所有,未經書面許可不准擅自傳閱、复制和修改。本公司保留法律追究的权利。

类别	针座	品名	CS-5333-08(带壳)	X.	±0.50
版本	A/0	设计	李文畅	X.X	±0.40
制定部门	工程部	绘制	李文畅	X.XX	±0.30
工程图号	CST-5333	审核	姚培柱	X.XXX	±0.20
制定日期	2018/04/11	核准	周中湖	X.XXXX	±0.10

材料		单位	mm
颜色		比例	1:1
画法		数量	
CST 深圳市永丰盈电子有限公司 ShenZhenYongFengYing ELEECTRONICS CO., LTD.			

SHEET 1 OF 1		
	修改内容	修改日期