

## SOT-23








### Features

- ✧ Low turn-on voltage
- ✧ Fast switching
- ✧ PN junction guard Ring for transient

### Mechanical Data

- ✧ Case: SOT-23, Molded plastic
- ✧ Marking & Polarity: See diagram below
- ✧ Weight: 0.008 grams (approx.)



### Maximum Ratings $T_A=25^{\circ}\text{C}$ unless otherwise specified

Type Number	Symbol	BAS40	Units
Peak Repetitive Reverse Voltage	VRRM	40	V
Working Peak Reverse Voltage	VRWM		
DC Blocking Voltage	VR		
Forward Continuous Current (Note 1)	IFM	200	mA
Non-Repetitive Peak Forward Surge Current @ $t \leq 1.0\text{s}$	IFSM	600	mA
Power Dissipation (Note 1)	Pd	200	mW
Thermal Resistance Junction to Ambient Air (Note 1)	$R_{\theta JA}$	357	$^{\circ}\text{C}/\text{W}$
Operating Junction Temperature Range	$T_J$	-55 to + 125	$^{\circ}\text{C}$
Storage Temperature Range	$T_{STG}$	-65 to + 150	$^{\circ}\text{C}$

### Electrical Characteristics

Type Number	Symbol	Min	Typ	Max	Units
Reverse Breakdown Voltage $I_R=10\mu\text{A}$	$V_{(BR)}$	40	-	-	V
Reverse Leakage Current $t_p < 300\mu\text{s}$ , $V_R=30\text{V}$	$I_R$	--	20	200	nA
Forward Voltage Drop $t_p=300\mu\text{s}$ , $I_F=1.0\text{mA}$ $t_p < 300\mu\text{s}$ , $I_F=40\text{mA}$	$V_F$	--	-	380 1000	mV
Junction Capacitance $V_R=0$ , $f=1.0\text{MHz}$	$C_j$	-	4.0	5.0	pF
Reverse Recovery Time (Note 2)	$t_{rr}$	-	--	5.0	nS

Notes: 1. Valid Provided that Terminals are Kept at Ambient Temperature.

2. Reverse Recovery Test Conditions:  $I_F=I_R=10\text{mA}$ ,  $I_{rr}=1.0\text{mA}$ ,  $R_L=100\Omega$ .

### RATINGS AND CHARACTERISTIC CURVES (BAS40 / -04 / -05 / -06)

FIG.1- POWER DERATING CURVE




FIG.2- MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT PER LEG




FIG.3- TYPICAL FORWARD CHARACTERISTICS




FIG.4- TYPICAL REVERSE CHARACTERISTICS




FIG.5- TYPICAL TOTAL CAPACITANCE VS REVERSE VOLTAGE





FIG.6- TYPICAL TRANSIENT THERMAL CHARACTERISTICS



PACKAGE	SPQ/PCS	CARTON SPQ/PCS	CARTON SIZE/CM	CARTON GW/KG	CARTON NW/KG
SOT-23	3000/REEL	90000	40X20X22	5.00	4.00