



■ Specifications :

- Voltage rating: 125V AC / DC
- Current rating: 1A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: $\geq 100M\Omega$
- Contact resistance: $\leq 20m\Omega$
- After environmental testing: $\leq 40m\Omega$

X1002 T- P XX

- ① Series No.
- ② Category : T-terminal
- ③ Material: P-Phosphor bronze
- ④ Plating Style:
 V01-All Gold Flash
 SN-Bright tin plating 70u";30u" Ni
 SN2-50u" Ni Min, 120u" Tin Min

X1002T-PSN2				Stamping Before Plating 50u" Min Ni, 120u" Sn Min	
X1002T-PV01	Phospho Bronze	AWG#28-32	0.92mm	Stamping Before Plating 30u" Ni/Whole Gold/Gold Flash	X1002H-A, X1002H-B
X1002T-PSN				Stamping Before Plating 30u" Ni/70u" Sn	
PART No	Material	Wire Range	Insulation O.D.	Finish	Suitable XKB Terminal

广东星坤科技股份有限公司

生效

ΔX	日期
ΔX	日期
ΔX	日期
MARK	DESCRIPTION

REVISIONS

UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE: X1002T-XXX
DWN	DATE	VIEW:	PART NO.: 1.0mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0

文件工程章

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn