







SPECIFICATIONS

Rated Current:3.0AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:1000V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°C to +105°C

Contact Material:Brass
 Contact Plating:Au or Sn Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PBT
 Max.Processing Temp: 180°C for 30-60 seconds
 (200°C for 10 seconds)

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



				OPERATION		DRAW	YiYuSheng	12.03.28	SCALE	FIT	深圳市华灿天禄电子有限公司 PART NO. PM254-1-N-W-8.5 TITLE: 2.54PF H8.5mm 1xNpin 180° W2.5mm	
				X.X	±0.30				UNIT	mm		
				X.XX	±0.20	CHECK		SIZE	A4			
				X.XXX	±0.10	APPROVE		SHEET	1/1			
A0	2012.03.28	NEW DRAWING		Angle	±3°			PROJ.				
REV	DATE	MODIFICATION DESCRIPTION		CHANGE	DIM	TOL						