



规格 Specification

- *电气特性 Electrical Characteristics:
 - 触点额定电流 Contact Current Rating:0.5Amperes.
 - 耐电压 Dielectric Withstanding Voltage:AC500V r.m.s.
 - 绝缘电阻 Insulation Resistance:1000 Megohms Minimum At DC 500V.
 - 接触电阻 Contact Resistance:100 mΩ Maximum.
- *机械特性 Mechanical Characteristics:
 - 寿命 Mating Cyeles:10,000 Cycles.
- *环境 Environmental:
 - 工作温度 Operating Temperature:-25°C~+85°C.
- *材料 Materials:
 - 绝缘子 Insulator:HI-Temp plastic UL 94V-0 Rated.
 - 触点 Contact:Copper Alloy.
 - 外壳 Shell:Stainless Steel(t=0.15mm).

Pin	Define
P1	SWITCH TERM CD
P2	DAT1
P3	DATO
P4	VSS
P5	CLK
P6	VDD
P7	CMD
P8	CD/DAT3
P9	DAT2
P10	GND
P11	GND
P12	GND



XKB Connectivity



PCB PATTERN LAYOUT
(GENERAL TOLERANCE:±0.05)

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES	DSND	DATE	SCALE: N/A	MODEL TYPE: TF CARD CONN		
ΔX					ANGLAR ±5°	DWN	DATE	VIEW:	PART NO.:		
ΔX					L ≤ 4 ±0.2	CHKD	DATE	UNIT: mm/in	DWG NO.:		
ΔX					4 < L ≤ 16 ±0.3	APPD	DATE	SIZE: A4	XKTF-1230-51		
ΔX					16 < L ≤ 63 ±0.4						
ΔX					L > 63 ±0.5						
						XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT 1.0g	SHEET 1/1	REVISION A0