

SPECIFICATION FOR APPROVAL

CUSTOMER		CUST P/N.		
ITEM	Radial Choke Inductor	Description	RL0608N-100K	
PART NO.	303-39581	DATE	2015.12.29	
			A	9.0 (Max) mm
			B	11.0 (Max) mm
			C	4.0 ± 0.5 mm
			D	3.5 ± 1.0 mm
			E	∅0.65 ± 0.1 mm
			F	mm
			G	mm
			H	mm

(2) ELECTRICAL REQUIREMENTS

TEST CONDITION		FREQUENCY	(3) TEST INSTRUMENTS		
			VOLTAGE	LCR-METER:	
L	10.0µH±10%	1KHz	0.25V		HP-4291A
				V	WB3260B
DCR	0.046Ω (Max)	KHz	V		DC RESISTANCE METER:
				V	WB3260B
IDC	1.5A (Max)	1KHz	0.25V		CURRENT SOURCE:
				V	TH2816B+1320
		KHz	V		RFIMPEDANCE/MATERIAL ANALYZER
					HP-4291A
		MHz	V		GW PUNCTURE INSULATION TESTER

(4) TURN: 19TS(REF)

(5) MATERIAL LIST

ITEM	MATERIAL	DESCRIPTION
1	CORE	SR60 DR6×8FSO
2	WIRE	∅0.5mm(2UEW)
3	TUBE	UL ∅7×10mm 印"10µH"
4		

REMARK:	APPROVED	CHECKED	DRAWN BY
	<i>Simon</i>	辛海峰	張小萍

MINGSTAR ELECTRONIC CORP.