


REV.	ECN NO.	APPD	DATE
A0	RELEASE	cheng	05/24'10
A1	倒钩孔尺寸加大到1.3	niezhenqi	06/23'14



B-810-XX21000-0*115
 NO. of Positions 10~64
 Color 0:Black 8:Grey

NOTES:
 1. Material:
 Insulator: PBT+30%GF, UL 94V-0,
 Color: Black or Grey.
 2. TEMPERATURE RANGE: -25°C TO + 85°C.

X ±0.5	UNITS	NAME:
.X ±0.38	MM	2.54mm Crimp Type IDC Housing
.XX ±0.25	MAT'L	PART NO.:
.XXX ±0.08	FINISH	B-810-**21000-0*115
.X' ±2'		APPD: JEFF 06/23'14
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF JUNHAD ENGINEERING CO.,LTD. AND SHALL NOT BE REPRODUCED COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF JUNHAD ENGINEERING CO.,LTD.		CHKD: JEFF 06/23'14
		DR: niezhenqi 06/23'14

nexttron 正凌精密工业股份有限公司
 NEXTRONICS ENGINEERING CORP

TITLE: 2.54mm Crimp Type IDC Housing
 DWG NO.: B-810-2021000-08115

SCALE	SHEET	REV.
1:1	1/1	A1