





RoHS

SPECIFICATIONS

Rated Current:3.0AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:1000V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°C to +105°C

Contact Material:Brass
 Contact Plating:AuIU Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PA6T
 Max.Processing Temp: 230°C for 30-60 seconds
 (260°C for 10 seconds)



Dimension antitheses list				
ITEM	PA	PB	PC	L
Standard	10.90	4.30	3.00	18.70
Alternate				

				OPERATION		DRAW		SCALE	FIT	深圳市连盛精密连接器有限公司		
				X.X	±0.30			UNIT	mm			
				X.XX	±0.20	CHECK		SIZE	A4	PART NO.		PH-01670
				X.XXX	±0.10			SHEET	1/1	TITLE:		2.54PH 2.5mm 1X5 90°
				Angle	±3°	APPROVE		PROJ.				
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL							