




(RECOMMENDED/P.C.B)HOLE LAYOUT  
COMPONENT SIDE VIEW TOLERANCE:±0.05



**G-Switch Specification**

- Material  
Housing:Hi-temp plastic ul 94v-0;black  
Contact:Copper alloy  
Shell:Stainless steel
- Electrical characteristics  
Contact current rating:0.5 amperes.  
Dielectric withstanding voltage:Ac500v r.m.s.  
Insulation resistance:500 mw min.  
Contact resistance:40 mw max.
- Environmental  
Operating temperature:-40°c~+90°c
- Environmental  
Mating cycles:5000 insertions
- Mechanical characteristics  
Card push insertion/out force:0.7~1.20kgf  
Contact separation force:0.20kgf min.

No.	ASSIGNMENT
1#	DAT2
2#	CD/DAT3 <sup>2</sup>
3#	CMD
4#	VDD
9#	CD
5#	CLK
6#	VSS
7#	DAT0
8#	DAT1



**b-Switch** 品赞科技®

Unless otherwise specified, Tolerance:  
 X. ±0.30  
 X.x ±0.20  
 X.xx ±0.15  
 X.xxx ±0.10  
 Angles ±3°

6	外壳	SUS304 T=0.15mm~ 镀镍底30u" 侧脚镀金0.5U"~平脚	1PCS
5	拉杆	SUS304~去磁	1PCS
4	滑块	LCP 黑色	1PCS
3	弹簧	SWP-B	1PCS
2	端子	C5191 T=0.15 镀Ni30U", 镀雾锡80U" 接触区域镀金1U"	1PCS
1	主体	LCP 黑色	1PCS
No.	品名	规格	数量

**G-Switch Electronic (HongKong) CO.,Ltd.**

DESIGN	陈锋枫	DATE	2022.08.24	TITLE:					
CHECKED		DATE		GT-TF003-H0185-02					
APPROVED		DATE							
http://www.dg-switch.com				REV.:	X1	SCALE:	4:1	UNIT:	mm
TEL:0769-82388879				SIZE:	A4	SHEET:	1/1		