



Top view

Recommended P.C.B Layout

MATERIAL

△ Insulator : NY6T,UL94 V-0
Contact Pin : Brass

SPECIFICATION

Current Rate : 3 AMP
Insulation Resistance : 5000MΩMin. at DC 500V
Contact Resistance : 20mΩMax. at DC 100mA
Dielectric Voltage : AC 500V for one minute
Operation Temperature : -40°C to + 105°C
适用波峰焊制程温度; 260°C±5°C 3~5s

210-9 1- 03 G B 01
1 2 3 4 5 6

1. 7: Green Product
9: Green Product High Temp
2. 1: Single row
2: Dual rows
3. No. of contacts per row
4. G: Gold flash
S: Selective
T: Tin plated
5. B: Black Insulator
W: White Insulator
6. Pinrex internal code.



G	修正材質, NY9T-->NY6T	2018/05/23	TOLERANCE .0 =±.30 .00 =±.20 .000 =±.XXX .0000=±. ANG.=±3'		OLD PART NO.		TITLE		
F	ADD DESCRIPTION	2013/06/18			UNITS : mm	DRAWER 楊海琴		PIN HEADER 2.54*2.54mm STRAIGHT TYPE, SINGLE ROW	
E	ADD SIZE	2013/01/28		SCALE NONE	SIZE A4	SHEET 1 OF 1	REV. G	APP'D 李劍	频锐科技股份有限公司 PINREX TECHNOLOGY CORP.
D	ADD DESCRIPTION	2012/09/07							
C	REVISE SIZE	2011/06/13							DRAW NO.
REV.	DESCRIPTION	DATE						210-91-03GB01	210-91-03GB01(G版)