



Recommended P.C.B Layout

MATERIAL
 ⚠ Insulator: NY6T UL94-V0
 Contact Pin : Brass

SPECIFICATION
 Current Rate : 3 AMP
 Insulation Resistance : 5000MΩMin.
 Contact Resistance : 20mΩMax.
 Dielectric Voltage : AC 500V for one minute

610-9 2- 06 G B 00
 1 2 3 4 5 6

1. 5: Normal parts
- 7: Green Product
- 9: Green Product High Temp
2. 1: Single row
- 2: Dual rows
3. No. of contacts per row
4. G: Gold flash
- T: Tin plated
5. B: Black Insulator
6. Pinrex internal code.



			TOLERANCE	 UNITS : mm	OLD PART NO.	TITLE	頻銳科技股份有限公司 PINREX TECHNOLOGY CORP.			
C	增加材質	2017/11/20	.0 =±.30		DRAWER	CHECK		FEMALE HEADER 2.54*2.54mm STRAIGHT TYPE, DUAL ROWS HEIGHT 8.5mm		
B	ADD SIZE	2012/04/16	.00 =±.20	SCALE	SIZE	SHEET	REV.	APP'D	NEW PART NO.	DRAW NO.
A	RELEASE	2009/12/24	.0000=±.	NONE	A4	1 OF 1	C	李劍	610-92-06GB00	610-92-06GB00(C版)
REV.	DESCRIPTION	DATE	ANG.=±3'							