

Recommended P.C.B Layout

MATERIAL



Insulator : 30% Glass fiber PBT
Contact Pin : Brass

SPECIFICATION

Current Rate : 3 AMP
Insulation Resistance : 5000MΩMin. at DC 500V
Contact Resistance : 20mΩMax. at DC 100mA
Dielectric Voltage : AC 500V for one minute
Operation Temperature : -40°C to + 105°C

210-7 2- 03 G B 01
1 2 3 4 5 6

1. 5: Normal Parts
- 7: Green Product
- 9: Green Product High Temp
2. 1: Single row
- 2: Dual rows
3. No. of contacts per row
4. G: Gold flash
- S: Selective
- T: Tin plated
5. B: Black Insulator
6. Pinrex internal code.

				TOLERANCE		 OLD PART NO. PH1S-203GB1160		TITLE		 頻銳科技股份有限公司 PINREX TECHNOLOGY CORP.
B	REVISE DIMENSIONS	2010/06/17	.0 =±.30	UNITS : mm	DRAWER	CHECK	PIN HEADER 2.54*2.54mm STRAIGHT TYPE, DUAL ROWS			
B	ADD DIMENSIONS	2005/09/14	.00 =±.20	SCALE	Age		NEW PART NO.		DRAW NO.	
A	RELEASE	2004/01/15	.000 =±.XXX	NONE	1 OF 1	REV. C	210-72-03GB01			210-72-03GB01(C版)
REV.	DESCRIPTION	DATE	ANG.=±3'	SIZE						
				A4						