

电气性能/Electrical

参考标准/Standard: UL IEC
 额定电压/Rated voltage: 300V 750V
 额定电流/Rated current: 20A 32A
 使用线径/Wire range: 22-12AWG 4.0mm²
 耐电压/Withstanding voltage: AC2000V/1Min
 绝缘电阻/Insulation resistance: 500MΩ/DC500V

机械性能/Mechanical

温度范围/Temp.Range: -40°C~+105°C
 最大锁紧力矩/Max.Talue: 1.2Nm(10.6lb. in)


尺寸/Dimensions

间距/Pitch: 9.5mm
 极数/Poles: 2P-24P

材质及电镀/Material

塑件/Housing: PA66, UL94V-0
 螺丝/Screws: M4, steel Ni plated
 焊脚/Pin header: Brass, 0.8, Tin plated

订购方式:
HOW TO ORDER



TOLERANCES EXCEPT AS NOTED

		linear dimension				fillet	chamfer		short angle sid				≡	—	□	//	⊥
variable range	to	over 6 to 30	over 30 to 120	over 120 to 480	all	to 6	to 10	to 10	to 30'	to 50	to 120	all	to 5	to 30	to 120	to 120	
tolerance	±0.1	±0.2	±0.3	±0.5	±0.9	±0.2	±0.5	±1	1'	30'	20'	10'	0.5	0.025	0.06	0.12	0.4

单位/UNITS	mm	尺寸/SIZE	A4	比例/SCALE	第一视角/FIRST ANGLE PROJECTION	
Cixi Dibo Electronics Co.,LTD					名称/NAME	
					DBT50G-9.5-XXP	