


NOTE:
 Operating Force:
 lever portion 70 ± 40 gf
 Push portion 200 ± 40 gf



| ITEM | PAPT NAMF | TER,NO | QTY | MATERIAL | FINISHING | REMARK |
|------|-----------|--------|-----|------------|----------------|--------|
| ⑥ | Terminal | — | 8 | Brass | Plating silver | — |
| ⑤ | Contact | — | 1 | F.ag/Brass | Plating silver | — |
| ④ | Base | — | 1 | Pa46 | — | — |
| ③ | Spring | — | 1 | Sus | Natural | — |
| ② | Cover | — | 1 | Sus | Natural | — |
| ① | Keystake | — | 1 | Pa46 | — | — |

| MARK | DESCRIPTION | DATE | REVISED | APPROVED | UNSPECIFIED TOLERANCES | DSND | DATE | SCALE: N/A | MODEL TYPE: MULTI-FUNCTIONAL SWITCH |
|------|-------------|------|---------|----------|------------------------|--------------------------------------|------|------------|--|
| ΔX | | | | | ANGLAR ±5° | DWN | DATE | VIEW: | PART NO.: |
| ΔX | | | | | X.X ±0.2mm | CHKD | DATE | UNIT: mm | DWG NO.: |
| ΔX | | | | | X.XX ±0.1mm | APPD | DATE | SIZE: A4 | TM-1011A |
| | | | | | X.XXX ±0.05mm | XKB INDUSTRIAL PRECISION CO.,LIMITED | | | WEIGHT 1.0g |
| | | | | | | | | | SHEET 1/1 |
| | | | | | | | | | REVISION A0 |