



PART NO.	H
TM-T07A-1	8.3
TM-T07A-2	8.5
TM-T07A-3	8.7
TM-T07A-4	9.3
TM-T07A-5	11.0
TM-T07A-6	12.3
TM-T07A-7	13.7

ITEM	PAPT NAMF	TER,NO	QTY	MATERIAL	FINISHING	REMARK
⑤	Contact Spring	—	1	Phosphor Bronze	Plating silver	—
④	Terminal	—	4	Phosphor Bronze	Plating silver	—
③	Base	—	1	Nylon		—
②	Cover	—	1	Nylon		—
①	Keystake	—	1	Nylon		—

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES	DSND	DATE	SCALE: N/A	MODEL TYPE: DETECT SWITCH
ΔX					ANGLAR ±5°	DWN	DATE	VIEW:	PART NO.:
ΔX					X.X ±0.2mm	CHKD	DATE	UNIT: mm	DWG NO.: TM-T07A-X
ΔX					X.XX ±0.1mm	APPD	DATE	SIZE: A4	WEIGHT
					X.XXX ±0.05mm	KXB INDUSTRIAL PRECISION CO.,LIMITED			SHEET
									1/1
									REVISION
									A0