



PAPT NO	TM-4175-X-X	
Operating force	A	4 Direction 180±50gf Center 250±50gf
	B	4 Direction 240±50gf Center 360±50gf
Height	H: A: 5 B: 6	

ITEM	PAPT NAMF	TER,NO	QTY	MATERIAL	FINISHING	REMARK
⑥	Terminal	6	6	Brass	Plating silver	
⑤	Contact	1	1	F.ag/Brass	Plating silver	
④	Base	—	1	Pa46		
③	Spring	—	10	Sus	Natural	
②	Cover	—	1	Sus	Natural	
①	Keystake	—	1	Pa46		

△X					ANGLAR	±5°	DSND		DATE	SCALE: N/A	MODEL TYPE: MULTI-FUNCTIONAL SWITCH	
△X					X.X	±0.2mm	DWN		DATE	VIEW:	PART NO.:	
△X					X.XX	±0.1mm	CHKD		DATE	UNIT: mm	DWG NO.:	
MARK	DESCRIPTION	DATE	REVISED	APPROVED	X.XXX	±0.05mm	APPD		DATE	SIZE: A4	TM-4175-X-X	
REVISIONS						UNSPECIFIED TOLERANCES	XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn										1.0g	1/1	A0