


TER	ANG	0° (NO)			
		(20°)	(15°)	(15°)	(20°)
①		▨			
②				▨	
③		▨	▨	▨	▨


CCW ————— CW

CODE TABLE



Circuit Diagram

NOTE:  
Operating Force.  
lever portion 100 ± 30 gf  
Push portion 205 ± 50 gf



# SWITCH CONNECTOR

ITEM	PART NAME	TER,NO	QTY	MATERIAL	FINISHING	REMARK
⑥	Terminal		4	Brass(0.15t)	Plating silver	
⑤	Contact		1	F.ag/Brass	Plating silver	
④	Base		1	Nylon		
③	Spring		1	Sus	Natural	
②	Cover		1	Sus	Natural	
①	Keystake		1	Nylon		

MARK	DESCRIPTION	DATE	REVISED	APPROVED	ANGULAR	±5°	DSND	DATE	SCALE: N/A	MODEL TYPE:		
ΔX					X.X	±0.2mm	DWN	DATE	VIEW:	MULTI-FUNCTIONAL SWITCH		
ΔX					X.XX	±0.1mm	CHKD	DATE	UNIT: mm	PART NO.:		
ΔX					X.XXX	±0.05mm	APPD	DATE	SIZE: A4	DWG NO.: <b>TM-2024A</b>		
REVISIONS							UNSPECIFIED TOLERANCES			XKB INDUSTRIAL PRECISION CO.,LIMITED		
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn										WEIGHT	SHEET	REVISION
										1.0g	1/1	A0