



■ Specifications(规格) :


- Voltage rating(额定电压): 500V AC / DC
- Current rating(额定电流): 2A AC / DC
- Withstanding voltage(耐压值): 1500V AC/minute
- Temperature range(工作温度): -40°C~+85°C
- Insulation resistance(绝缘电阻): $\geq 1000M\Omega$
- Contact resistance(接触电阻): $\leq 30m\Omega$
- After environmental testing(环境测试后): $\leq 40m\Omega$



X3700H-02-PT

① ② ③ ④

- ① 系列
- ② 类别: H-HSG
- ③ PIN数或防呆KEY形态: 单排-XX
- ④ 材质: PA66, UL94V-0



X3700H-02-PT	PA66 UL94V-0	X3700T	X3700W
PART NO	Material	Suitable XKB Terminal	Suitable XKB Terminal

For and on behalf of
XKB INDUSTRIAL PRECISION CO., LIMITED
香港星坤工業精密有限公司

△ X					ANGULAR	±5°
△ X					L ≤ 4	±0.2
△ X					4 < L ≤ 16	±0.3
MARK	DESCRIPTION	DATE	REVISED	APPROVED	16 < L ≤ 63	±0.4
					L > 63	±0.5
					UNSPECIFIED TOLERANCES	

DSND		DATE		SCALE: N/A	MODEL TYPE: X3700H-02-PT	
DWN		DATE		VIEW:	PART NO.:	
CHKD		DATE		UNIT: mm	3.70 mm Crimp Style connectors	
APPD		DATE		SIZE: A4	DWG NO.:	
				WEIGHT	SHEET	REVISION
				1.0g	1/1	A0

Authorized Signature(s)

XKB INDUSTRIAL PRECISION CO., LIMITED