

1 2 3 4 5 6 7 8

A

B

C

D

E

F

A




B

C


D

E

F



0.1
SMT 贴面





■ Specifications :

- Voltage rating: 500V AC / DC
- Current rating: 2A AC / DC
- Withstanding voltage: 1500V AC/minute
- Temperature range: -40°C~+85°C
- Insulation resistance: ≥1000MΩ
- Contact resistance: ≤40mΩ
- After environmental testing: ≤80mΩ

X3700 W M-02HF-LPSN

① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No
- ② Category: W-WAFER
- ③ Welding Board Angle: M-Male
- ④ Row No.-Pin No.: 02-Single Row
- ⑤ Plug the Pin & Special No.: HF-Halogen Free
- ⑥ Material: LP -LCP 94V-0
- ⑦ Plating Category: SN-Bright Tin Plating



X3700WM-02HF-LPSN	LCP UL 94V-0 Halogen Free	Phosphor Bronze	Matte Tin-Plated	Phosphor Bronze	Matte Tin-Plated	X3700WF
PART NO	Material	Material(Pin)	Finish(Pin)	Material (Solder Tab)	Finish (Solder Tab)	Mates With Housing

For and on behalf of
XKB INDUSTRIAL PRECISION CO., LIMITED
香港星坤工業精密有限公司

△ X					ANGULAR	±5°	
△ X					L ≤ 4	±0.2	
△ X					4 < L ≤ 16	±0.3	
△ X					16 < L ≤ 63	±0.4	
MARK					L > 63	±0.5	
	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES		
	REVISIONS					Authorized Signature(s)	

DSND		DATE		SCALE: N/A	MODEL TYPE: X3700WM-02HF-LPSN
DWN		DATE		VIEW:	PART NO.:
CHKD		DATE		UNIT: mm	3.70mm BTB Style Connectors
APPD		DATE		SIZE: A4	DWG NO.:
					WEIGHT
					1.0g
					SHEET
					1/1
					REVISION
					A0

XKB INDUSTRIAL PRECISION CO., LIMITED

1 2 3 4 5 6 7 8