




- NOTE:
1. Rating : DC 5V 10mA
 2. Contact Resistance: 100mΩMAX
 3. Insulation Resistance: 100MΩMIN
 4. Soldering Temper: 260±5°/5s
 5. Mechanical Life: 100,000 cycles
 6. Ever Portion 80 ± 50 gf
 7. Push Portion 205 ± 80 gf
 8. Travel: -24° 0° +24°

A向24° a与b

B向24° a与d

C向150g
a与c通



ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑤	Spring	—	1	SUS	Natural	—
④	Terminal	—	5	Phosphor Bronze	Plating silver	—
③	Cover	—	1	SUS	Natural	—
②	Base	—	1	LCP	Black	—
①	Keystroke	—	1	PPA	Black	—

APPROVALS	DATE
DRAWN KUN,LU	2013/8/8

CHECKED	TITLE:
	MULTIFUNCTIONAL SWITCHS

APPROVALS	PART NO.	SCALE:	PROJ:
	K1-1502SA-04	1:1	

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

TOLERANCES ARE	ANGLE	UNIT:	DRAWING NO.	SHEET
30~12.5 ±	±0.30	mm		1 OF 1
10~30 ±0.20	±0.15			
5~10 ±0.15	±2'			
~5 ±0.10				



ELECTRONICS CO.,LTD