




Circuit Diagram



PCB Layout(Pattern side)

NOTE:
 Rating: DC 20V 50mA
 Operating Force: 20±10gf
 Lifetime: 100,000 Cycles

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑤	Spring	—	1	SUS	Ag Plated	—
④	Terminal	—	4	Phosphor Bronze	Ag Plated	—
③	Cover	—	1	PA46	Black	—
②	Base	—	1	PA46	Black	—
①	Slider	—	1	PA46	Black	—

APPROVALS	DATE	TITLE:
DRAWN J.X.Zhang	2013/9/22	DETECTOR SWITCHS
CHECKED		ELECTRONICS CO.,LTD
APPROVALS		

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.																
	A		NEW																			
<table border="1"> <thead> <tr> <th>TOLERANCES ARE</th> <th>±0.30</th> <th>±0.20</th> <th>±0.15</th> <th>±2°</th> <th>DRAWING NO.</th> <th>PROJ.</th> <th>SHEET</th> </tr> </thead> <tbody> <tr> <td>30~12.5</td> <td>10~30</td> <td>5~10</td> <td>~5</td> <td></td> <td></td> <td>K5-1616SA-02</td> <td>1 OF 1</td> </tr> </tbody> </table>							TOLERANCES ARE	±0.30	±0.20	±0.15	±2°	DRAWING NO.	PROJ.	SHEET	30~12.5	10~30	5~10	~5			K5-1616SA-02	1 OF 1
TOLERANCES ARE	±0.30	±0.20	±0.15	±2°	DRAWING NO.	PROJ.	SHEET															
30~12.5	10~30	5~10	~5			K5-1616SA-02	1 OF 1															