


# 深圳市连线电子有限公司

客户承认图

CUSTOMER(客户):立创	Customer Part NO(客户物品号):
	Part Descripon(物品规格): 0.5*13*75*A (44/88) (0.035*0.3)

Item	项目	Specification	规格值
NO. of conductors	导体芯数 N	13	
Pitch	间距 P	0.5±0.05	
Total Pitch	全间距 PT	6±0.05	
Total Length	总长度 L	75±2	
Insulation Length	绝缘长度 IL	67±2	
Margin Width	边缘宽度 M	0.5±0.07	
Total Width	总宽度 W	7±0.08	
Strip Length	线口长度 S1	4±1	
Strip Length	线口长度 S2	4±1	
Reinforeing tape length	补强板长度B1	8±2	
Reinforeing tape length	补强板长度B2	8±2	
Slanting	线口倾斜度 A	≤0.3	
Over lap	冲孔	/	
Terminal thickness	插入厚度 t1	0.303±0.05	
Thickness insulation	线身厚度 t	0.121±0.05	



Conductor thickness 导体厚度 Ct	0.035±0.005	印字内容: AWM 20624 80C 60V VW-1 颜色: 蓝色
-----------------------------	-------------	-------------------------------------

Conductor width 导体宽度 Cw	0.3±0.03	Storage condition:(储存条件) Recommended(推荐)
-------------------------	----------	--

Supporting Tapc Color 补强板颜色	(Blue)蓝色	Temp: 15°C~25°C(温度15°C~25°C)Humidity: 30~60RH%(湿度30~60RH%)
-----------------------------	----------	--

PET(Supporting Tapc Color)补强板规格	0.225mm	Drawing Not To Scale Hidden Lines Not Shown 图规不能以其线材比来 衡量, 隐藏线不显示
PET(Insulation) 绝缘胶规格	0.043mm (有印字)	
PET(Insulation) 绝缘胶规格	0.043mm (无印字白色)	
Rev 版本	A1	

Discharge Date 发行日期	Review Date 修订日期	Drawing NO 图纸编号
2017.09.08		20170908-001
Drawing by 制图	Checked by 核对	Approved by 确认
lilyen		

