



备注:

1. 材质:
  - 1.1 胶芯: LCP UL94V-0;
  - 1.2 端子: 磷铜, 镍底 50μm, 全金 1μm;
  - 1.3 外壳: SUS, 镍底 50μm, 焊接脚镀金 1μm;
2. 主要特性:
  - 2.1 额定电流: 0.5A;
  - 2.2 接触阻抗: 50mΩ MAX;
  - 2.3 绝缘阻抗: 100MΩ MIN 100V DC;
  - 2.4 耐压测试: 100V AC;
  - 2.5 沾锡性: 温度 235 ± 5℃, 时间 5 ± 0.5s;
  - 2.6 单PIN 正向应力: 0.035kgf MIN;
  - 2.7 使用寿命: 5000次;
  - 2.8 耐温性: 烤箱测试: 温度 250 ± 5℃, 时间 2分钟;
  - 2.9 工作环境: 温度: -30℃ ~ +80℃; 湿度: 80% MAX;



Recommended PCB Layout



PIN 脚 定 义

第1PIN	第2PIN	第3PIN	第4PIN	第5PIN	第6PIN
VCC	RESET	CLK	GND	VPP	I/O

UNLESS OTHERWISE SPECIFIED TOLERANCE			
UNIT:	DECIMAL	LINEAR	ANGLES
mm	X.	±0.50	±5°
	X.X	±0.25	±3°
	X.XX	±0.12	±1°

东莞市讯普电子科技有限公司

www.xunpudianzi.com

DRAWN NAME: SIM CONNECTOR

PRODUCT NO. SIM-104

DRAWN	Fros	2014/12/12
CHECKED	Ron	2014/12/12
APPROVED	Albert	2014/12/12
SCALE	3.2	SHEET 1/1
SIZE	A4	