





Recommended PC board pattern
(TOP VIEW)



SPECIFICATIONS

- 1.CURRENT RATING: 2.0A AC/DC.
- 2.VOLTAGE RATING 100V AC/DC.
- 3.TEMPERATURE RANGE:-55°C TO +125°C
- 4.CONTACT RESISTANCE: INITIAL VALUE/30mΩ MAX.
AFTER ENVIRONMENTAL TESTS/60mΩ MAX.
- 5.INSULATION RESISTANCE:300 MΩ MIN.
- 6.WITHSTANDING VOLTAGE:500V AC/MINUTE.




TABLE	NO OF ROWS	A	B	C	D
H	4x5	8.89	6.85	5.08	7.87
6.35	4x10	15.24	13.2	11.43	14.22
8.00	4x15	21.59	19.55	17.78	20.57
10.00	4x20	27.94	25.9	24.13	26.92
12.00	4x25	34.29	32.25	30.48	33.27
	4x30	40.64	38.6	36.83	39.62
	4x35	46.99	44.95	43.18	45.97
	4x40	53.34	51.3	49.53	52.32
	4x45	59.69	57.65	55.88	58.67
	4x50	66.04	64.00	62.23	65.02

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CANKEMENG INDUSTRIAL CO., LTD			
CHECKED:	DATE:	TITLE: BTB1.27-4*15P 母座 立贴 塑高4.57(合高8.0)			
DRAWN: YKX	DATE: 2026-7-7	PART. NO.	Z-BTB1260P-F401		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-BTB-E001		REV. A LXW0

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05