








RECOMMENDED PCB LAYOUT

规格说明:Specifications:

电气特性:Electrical:

- 额定电流: Current Rating
1.0A/contact terminal
- 额定电压: Voltage Rating
30V DC
- 接触阻抗: Contact Resistance
50 milliohms MAX
- 耐电压: Dielectric Withstanding Voltage:
300 V AC AT Sea Level
- 绝缘阻抗: Insulation Resistance:
100MEGA ohms MIN

物理性能: Mechanical:

- 插拔力: Connector Mate and Unmate Force
Mate force: 3.0kgf (MAX)
Unmate force: 0.7kgf (MIN)
- 端子保持力: Terminal Retention
0.5kgf (MIN)

原材料: Material:

- 塑胶: Housing:
Hing Temperature Tnermaplastics,
Ul 94V-0 LCP Black
- 端子: Contact: Copper Alloy C2680/C5191
- 外壳: Shell: Copper Alloy C2680

电镀: Finish:

- 端子: Contact: Plated Gold in Mating Area;
Tin On Solder Talls
- 外壳: Shell:
Nickel Plating

使用温湿度环境: -30 °C~+85 °C

储存温湿度环境: -40 °C~+60 °C

深圳市金航标电子有限公司 www.kinghelm.com.cn 0755-28190160		图号 (DWG NO)		单位 (UNIT): MM
		版本 (REV)	A/0	比例 (SCALE) 1: 1
品名 (ITEM NO)	MINI USB 5P/F SMT (B型 0.3T, 0.6柱)	日期 (DATE)	2009.11.16	 未注公差 TOLERANCE UNSPECIFIED X.X ±0.30 X.XX ±0.20 X.XXX ±0.10 X° ±5° X.X° ±2°
料号 (PART NO)	KH-MINI-SMT-5P-CU-SMT	设计 (DESIGN)	刘文龙	
模号 (MODEL NO)	A036-2B-1	审核 (CHECKED)		
		核准 (APPROVED)		