

RoHS

REV.

ECN.#

DESCRIPTION

NAME

DATE

A0

NEW RELEASE

HZP


2023.01.02

NOTES:

SPECIFICATION:

1. CURRENT RATING: 6.0A MAX
2. VOLTAGE: 100 VAC
3. TEMPERATURE RANGE: -30 °C ~ 85 °C
4. CONTACT RESISTANCE: 40 MILLIONHM MAX
5. INSULATION RESISTANCE: 100 MEGOHMS MIN.
6. LNSERTION FORCE : 5N~20N
7. UNMATING FORCE: 8N~20N
8. DURABILITY: 10,000 CYCLES

RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED $\pm 0.05\text{mm}$



10	POTTING	SILICONE	BLACK	1PCS
9	UPPER SHELL	STAINLESS STEEL	Ni Plated	1PCS
8	LOWER SHELL	STAINLESS STEEL	Ni Plated	1PCS
7	MAIN SHELL	STAINLESS STEEL	Cleansing	1PCS
6	OVER MOLDING	HIGH TEMPERATURE PLASTIC	BLACK	1PCS
5	TOP I/M	HIGH TEMPERATURE PLASTIC	BLACK	1PCS
4	BOTTOM I/M	HIGH TEMPERATURE PLASTIC	BLACK	1PCS
3	MID PLATE	STAINLESS STEEL	Ti/Ni Plated	1PCS
2	CONTACT-B	COPPER ALLOY	Au/Ni Plated	1SET
1	CONTACT-A	COPPER ALLOY	Au/Ni Plated	1SET
NO.	DESCRIPTION	MATERIAL	REMARKS	QTY

MILLIMETERS

INCH

X." $\pm 2^\circ$ X." $\pm 2^\circ$ X ± 0.30 X ± 0.012 XX ± 0.20 XX ± 0.008 XXX ± 0.10 XXX ± 0.004

THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF DongGuan JinBilal
Metal Plastic Technology Co.,Ltd
COPIED OR USED IN ANY MANNER WITHOUT THE
PRIOR WRITTEN CONSENT OF DongGuan
JinBilal Metal Plastic Technology Co.,Ltd



东莞市金比莱五金塑胶科技有限公司
DONGGUAN JBL TECH CO., LTD

TITLE

TYPE C 16P 防水母座 沉板
1.65 CH0.14 漏舌片 带螺丝孔

DR

PART NO.

1043114872

CHKD


PRO J.

PAGE 1/2 UNITS mm APPD

SIZE

A4 SCALE 1:1 DIS NO.

RoHS




COVER TAPE PEELING ANGLE: 165°~180°

PEELING FORCE: 20~130g

CARRIER TAPE

USER DIRECTION OF UNREELING


DETAIL B




DETAIL B

NOTES

1. NUMBER OF CONNECTORS: 1000PCS/REEL
2. LEAD TAPE LENGTH



3. QUANTITY: 8000PCS/CARTON



MILLIMETERS	INCH	 东莞市金比莱五金塑胶科技有限公司 DONGGUAN JBL TECH CO., LTD				
X.* ±2*	X.* ±2*					
.X ±0.30	.X ±0.012	TITLE	TYPE C 16P 防水母座 沉板		DR	
.XX ±0.20	.XX ±0.008		1.65 CH0.14 漏舌片 带螺丝孔			
.XXX ±0.10	.XXX ±0.004					
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd		PART NO.	1043114872		CHKD	
		PRO J.	PAGE	2/2	UNITS	mm
			SIZE	A4	SCALE	1:1
			DIS NO.			