








RoHS Compliant



RECOMMENED P.C.B LAYOUT (TOP VIEW)

GENERAL TOLERANCE ± 0.05



NOTES:

1,MATERIAL:

1-1.HOUSING:THERMOPLASTIC,UL94V-0,COLOR:WHITE;

1-2,CONTACT:COPPER ALLOY T=0.15MM;

1-3,SHELL:SUS, T=0.25mm

2,FINISH:

2-1.CONTACT:GOLD FLASH PLATING ON CONTACT AREA

AND SOLDER TAILS, Ni 50u" MIN. UNDERPLATING OVERALL;

2-2,SHELL: PLATING ALL OVER NICKEL 50u" Min.

3,SPECIFICATIONS:

3-1.VOLTAGE RATING: 100VAC

3-2.CURRENT RATING: PIN1/PIN5 3.0A Max

PIN2/PIN3/PIN4 1.0A Max

3-3.INSULATION RESISTANCE:100MEG.OHM MAX

3-4.CONTACT RESISTANCE:50 MILL.OHM MAX

3-5.OPERATION TEMPERATURE:-20°TO+65°

3-6.INSERT FORCE: 35N MAX

3-7.EXTRACT FORCE: 8N MIN

深圳市敏连达科技有限公司

Shenzhen Minlianda Technology Co.,Ltd.

品名(ITEM NO) MICRO USB 5P 6.4脚 平口

料号(PART NO) MLD-MICRO USB-ZB6.4

单位(UNIT): MM

未注公差

TOLERANCE UNSPECIFIED

版次(REV): A/0

页次(PAGE):1/1

设计 (DESIGN)

柯南

比例(SCALE) 1:1


X.X ± 0.38
X.XX ± 0.20
X.XXX ± 0.10
X" $\pm 5^\circ$
X.X" $\pm 2^\circ$

模号 (MODEL NO)

图号 (DWG NO)

审核 (CHECKED)

邱敏



MLD-2509031032

核准(APPROVED)

陈镇