










RECOMMEND PCB LAYOUT (T=1.2)
PCB TOLERANCE:±0.05

SPECIFICATION:

1.MATERIAL:

HOUSING: LCP UL 94V-0

COLOR: BLACK

CONTACT: PHOSPHOR BRONZE C5191R-H,T=0.25mm

PEG: BRASS C2680R-H,T=0.30mm

2.FINISH:

CONTACT:1u"3u"5u"15u" GOLD PLATING ON CONTACT AREA

100u" TIN PLATING ON SOLDER TAILS

30u" NICKEL UNDERPLATING OVER ALL

PEG:100u" TIN PLATING ON SOLDER TAILS

30u" NICKEL UNDERPLATING OVER ALL

环保要求

产品必须符合ROHS要求

制图
DRAWN

变更内容
DESCRIPTION

日期
DATE

GENERAL TOLERANCE

制图
DRAWING

ROSE

料号
PART NO.

ZX-SATA-03-22PXTMP2

版本
REV.

A

3

Peg

Brass C2680R-H

Tin/Ni Plated

2

Terminal

Pho.Bronze C5191R-H

Gold/Tin Plated

1

Housing

High Temp

Black

UL 94V-0

NO.

DESCRIPTION

MATERIAL

COLOR

REMARK

X.

±0.30

X.*

±3*

X.X

±0.20

X.X*

±2*

X.XX

±0.05

X.XX*

±0.5*

审核
CHECK

LEO

核准
APPROVAL

JOHN

单位
UNITS

MM

比例
SCALE

1:1



兆星精密电子(深圳)有限公司
ShenZhen ZhaoXing Precision electronics Co., Ltd.