










REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



SPECIFICATION

- 1.CURRENT RATING:1.5 AMP.
- 2.VOLTAGE RATING:125 VAC RMS.
- 3.INSULATION RESISTANCE:500 MEGOHMS MIN.
- 4.WITHSTAND VOLTAGE:
DC 500V RMS 50Hz or 60Hz MIN.
- 5.CONTACT RESISTANCE:40 MILLIOHMS MAX.
- 6.DURRABILITY:750 MATING CYCLES MIN.
- 7.MATING/UNMATING FORC:2.24 KG.F MAX.
- 8.OPERATION TEMPERATURE: -40℃~+85℃.
- 9.STORAGE TEMPERATURE:-40℃~+85℃.



PCBLAYOUT
TOL:±0.05

NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR	Remark
4	LED	2	TIN PLATING		
3	SHELL	1	C2680 T=0.2mm NI PLATING		
2	TERMINAL	8	C5191 T=0.25mm Au PLATING ON CONTACT AREA, TIN PLATING ON SOLDER AREA,NI PLATING ALL AREA.		
1	HOUSING	1	LCP UL94V-0 BLACK		

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.:±0.35	X':±3"	PART NO.	TITLE:		
X.X:±0.25	X.X':±2"	RJ45-5034-8P	RJ45 9.9H 面板1.1 DIP 有壳有灯		
X.XX:±0.15	X.XX':±1"	DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia		SCALE	SHEET
MATERILA	---	APPD: Ava		N:A	1/1
FINISH	---				