




技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100M\Omega$

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
		合高(H)	公座单高	母座单高
		1.5	1.3	1.4
		2.0	1.3	1.9
		2.5	1.3	2.4
Part No	CKT	A	B	C
BTB0513G-2*5PCL2	2X5	2.00	3.40	5.50
BTB0513G-2*6PCL2	2X6	2.50	3.90	6.00
BTB0513G-2*7PCL2	2X7	3.00	4.40	6.50
BTB0513G-2*8PCL2	2X8	3.50	4.90	7.00
BTB0513G-2*9PCL2	2X9	4.00	5.40	7.50
BTB0513G-2*10PCL2	2X10	4.50	5.90	8.00
BTB0513G-2*11PCL2	2X11	5.00	6.40	8.50
BTB0513G-2*12PCL2	2X12	5.50	6.90	9.00
BTB0513G-2*13PCL2	2X13	6.00	7.40	9.50
BTB0513G-2*14PCL2	2X14	6.50	7.90	10.00
BTB0513G-2*15PCL2	2X15	7.00	8.40	10.50
BTB0513G-2*16PCL2	2X16	7.50	8.90	11.00
BTB0513G-2*17PCL2	2X17	8.00	9.40	11.50
BTB0513G-2*18PCL2	2X18	8.50	9.90	12.00
BTB0513G-2*19PCL2	2X19	9.00	10.40	12.50
BTB0513G-2*20PCL2	2X20	9.50	10.90	13.00
.....	...	...	...	...
BTB0513G-2*50PCL2	2X50	24.50	25.90	28.00

序号	品名	材质	TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd				
①	0.5 Pitch C型 单槽立式BTB公座胶芯	LCP UL94 V-0 颜色:米黄色	X.±0.50	±1°	PART NO. BTB0513G-2*NPCL2	TITLE: 0.5 Pitch C型单槽 立式BTB公座业务图(单高1.3)			
			X.X±0.20						
			X.XX±0.10		DESIGN: Ethan	MANUFACTURE DWG			
②	0.5 Pitch C型 单槽立式BTB公座端子	铜合金/表面点镀金	UNITS	mm	CHED: Olvia				
			MATERILA	---					
			FINISH	---	APPD: Ava	SCALE N:A	SHEET 1/1		