









RECOMMENDED PCB LAYOUT
(TOL:±0.05)



Specifications

A. Material

Plastic cement: LCP, Black
Contact: Copper Alloy, T=0.15mm
Shell: Copper Alloy, T=0.30mm

B. Plating

Contact Area: 1u" Au over 50u' min. Nickel
Solder Tails: 1u" Au over 50u' min. Nickel
Shell: 60u" min. Nickel

C. Electrical

Current Rating: 1.0A/contact terminal
Voltage Rating: 30V
Power Rating: 30W
Contact Resistance: 40mΩ max initial
50mΩ max after test
Dielectric Withstanding Voltage: 100V AC
Insulation Resistance: 100MΩ min.

D. Mechanical & Environmental

Operating Temperature: -25° to +85°
Insertion force: 35.7 N Max
Withdrawal force: 8~20N
Durability: 3000 cycles


Pin Numbe	Signal Name
1	VBUS
2	D-
3	D+
4	ID
5	GND

Part Number			Product Description		
PMCFB-R22C-035			Micro USB Receptacle, Type B, Horizontal, 5 Pin, SMT, Bottom Mount, With Outer Shell Stakes		
DWG.No.	P-MCF-084		Tolerances Unspecified		Units: Metric(mm)
Revision	A0		X.X ±0.35	X° ±5°	
Designed	Lee	12/18/20	X.XX ±0.25	X.X° ±2°	
Approved	Allen	12/18/20	X.XXX ±0.15		




www.szywf.com.cn
www.szywf.cn


Sheet No. 1/2




1 Rubber disc




2 1000pcs/ disc



Product




3 10 plates/box (10 Kpcs)




LABEL

6 Paste the product or ROHS label as shown.



5 The outer box is sealed with transparent adhesive tape in the shape of "H".



4 Each case contains 10 plates, if the last few cases are filled with fillers.

Part Number			Product Description			
PMCFB-R22C-035			Micro USB Receptacle, Type B, Horizontal, 5 Pin, SMT, Bottom Mount, With Outer Shell Stakes			
DWG.No.	P-MCF-084		Tolerances Unspecified		Units: Metric(mm)	
Revision	A0		X.X	±0.35	X°	±5°
Designed	Lee	12/18/20	X.XX	±0.25	X.X°	±2°
Approved	Allen	12/18/20	X.XXX	±0.15		



Connecting the Future

www.szywf.com.cn
www.szywf.cn

Sheet No. 2/2