




RoHS

REV	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2026.07.27

- SPECIFICATIONS
1. Current rating: 1A AC, DC
 2. Voltage Rating: 250V AC/DC
 3. Temperature range: -40°C ~ +105°C
 4. Insulation resistance: 500MΩ Min.
 5. Withstanding voltage: 100V AC/ minute.
 6. Contact resistance: 20mΩ Max.

Material:
Insulator Material: PA6T (UL 94V-0)
Contact Material: Brass
Plating: Matte Tin or gold plated over Nickel
Mate with XFCN PZ127 Single row series

Ordering Code:
PM127V-11-XX-H43
1 2
1. 序列号
2. Pin位数: (02-50)

No. of Pin/Row	Dimension	
	A	B
02	1.27	2.94
03	2.54	4.21
04	3.81	5.48
05	5.08	6.75
06	6.35	8.02
07	7.62	9.29
08	8.89	10.56
09	10.16	11.83
10	11.43	13.10
11	12.70	14.37
12	13.97	14.64
13	15.24	16.91
14	16.51	18.18
15	17.78	19.45
16	19.05	20.72
17	20.32	21.99
18	21.59	23.26
19	22.86	24.53
20	24.13	25.80
21	25.40	27.07
22	26.67	28.34
23	27.94	29.61
24	29.21	30.88
25	30.48	32.15
26	31.75	33.42
27	33.02	34.69
28	34.29	35.96
29	35.56	37.23
30	36.83	38.50
31	38.10	39.77
32	39.37	41.04
33	40.64	42.31
34	41.91	43.58
35	43.18	44.85
36	44.45	46.12
37	45.72	47.39
38	46.99	48.66
39	48.26	49.93
40	49.53	51.20
41	50.80	52.47
42	52.07	53.74
43	53.34	55.01
44	54.61	56.28
45	55.88	47.55
46	57.15	58.82
47	58.42	60.09
48	59.69	61.36
49	60.96	62.63
50	62.23	63.90

X.±0.50	X.°±	PART NO: PM127V-11-XX-H43	XFCN 兴飞连接器			
.X±0.25	.X°±					
.XX±0.15	.XX°±		0769-82001899			
.XXX±0.10	.XXX°±		www.xfconn.com			
UNITS:	mm	TITLE: 1.27mm Female Header Connectors		DWG NO: /		
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN						
		APPD	Chen ZhiQiang			
		CHKD	Liu Wei	VIEW		
		DRAW	Chen HongJiang	SCALE	SHEET	REV
		DATE	2026.07.27	NONE	1/1	A1