



NOTES:

1.ELECTRICAL CHARACTERS

1-1.RATING: DC 9V 2.5A

1-2.CONTATCT RESISTANCE:<30mΩ

1-3.INSULATION RESISTANCE:≥100MΩ DC 500V:


1-4.WITHSTANDING VOLTAGE:AC 500V 1min;

1-5.LIFE:5.000 CYCLES ,

2.MECHANICAL CHARACTERISTICS,

2-1.INSERTION&EXTRACTION FORCE:3~30N;

2-2.OPERATING TEMPERATURE:-30 °C~+70 °C



PCB HOLES(TOP VIEW)

GENERAL TOLERANCE:0.1mm

⑤	TERMINAL	3	1	BRASS t=0.3	CuSn
④	BREAK TERMINAL	2	1	BRASS t=0.3	CuSn
③	TIP SPRING	1	1	MANGANESE STEEL	SnSb
②	COVER		1	PA66	BLACK
①	HOUSING		1	PPA	BLACK
No.	PART NAME	TER'NO.	QTY	MATERIAL	REMARK

广东星坤科技股份有限公司	
日期	日期
文件工程章	

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ANGLAR	±5°			
L ≤ 4	±0.2			
4 < L ≤ 16	±0.3			
16 < L ≤ 63	±0.4			
L > 63	±0.5			

DSND	SCALE: N/A	MODEL TYPE: DC POWER JACK
DWN	VIEW: ①	PART NO.: DC-003-2A-1.3
CHKD	UNIT: mm/in	DWG NO.:
APPD	SIZE: A4	
XKB INDUSTRIAL PRECISION CO.,LIMITED		WEIGHT
		SHEET 1/1
		REVISIC A0