







Specifications:

规格:

Voltage rating:150V AC/DC

额定电压: 150V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-25℃~+85℃

温度范围: -25℃~+85℃

Insulation resistance:≥500MΩ min

绝缘电阻: ≥500MΩ Min

Contact resistance:≤30mΩ Max

接触电阻: ≤30mΩ Max

X9812	W	V	S	2x10	6T	V01
①	②	③	④	⑤	⑥	⑦

- 1.Series No
- 2.Category:W-Wafer
- 3.Welding Board Angle:V-Stright 180°
- 4.Welding Way:S-SMT
- 5.Row No.Pin No:XX-2x05~2x25P
- 6.Material:6T-PA6T UL 94V-0 Natural
CAP:PA6T UL 94V-0 Natural
- 7.Plating:V01-Gold Flash

Poles	Dimensions(mm)	
	A	B
2x02	1.25	8.75
2x05	5.00	12.50
2x06	6.25	13.75
2x07	7.50	15.00
2x10	11.25	18.75
2x12	13.75	21.25
2x15	17.50	25.00
2x20	23.75	31.25

X9812WVS-2x10-6TV01	PA6T	Brass	X9812H
PART NO	Material	Material(Pin)	Suitable XKB Housing

DSND	SCALE: N/A	MODEL TYPE: 1.25mm Crimp Style Connector
DWN	VIEW:	PART NO.: X9812WVS-2x10-6TV01
CHKD	UNIT: mm/in	DWG NO.: X-X9812WVS-2x10-6TV01
APPD	SIZE: A4	WEIGHT
		SHEET
		REVISION
		1/1
		A0

					ANGLAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
ΔX					16 < L ≤ 63	±0.4
MARK					L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED