





General Specification
Current Rating:1.5A DC /Contact, 20mA DC for LED signals
Voltage Rating:125V AC /Contact, 2.0 volts DC for LED signals
Operating Environment
Standard Temperature: -20℃~+70℃
Industrial Temperature: -40℃~+85℃
Humidity: 20~70%
Contact Resistance: ≤30mΩ
Insulation Resistance: ≥500MΩ
Dielectric Strength:500V AC/(50HZ)/Min
Withstanding Voltage:500V AC/(50HZ)/Min
Durability:2000 Cycles Min

Material Specification
Housing :Thermoplastic, UL94V-0
Contact :Alloy Copper
Shield :Alloy Copper
Please refer to the customer drawing when customer has specified



PCB LAYOUT
(TOP VIEW)

网络插座外形图



温州瑞川电子有限公司
WEN ZHOU RUI CHUAN ELECTRONIC CO., LTD.

序号	名称	材料	数量	镀层/颜色	备注
4	LED	RESIN/Fe	8	NI	
3	插针	PHOSPHOR BRONZE	32	FU ⁰	
2	后盖	PBT	4	Yellow	
1	塑座	PBT	1	Yellow	

绘图:	吴家飞	日期:	2022.5.6
审核:	陈伟	日期:	
核准:	陈伟	日期:	

图号:	10~30	公差:	±0.20
角度:	~10	公差:	±0.15
版本:	1 of 1	版本:	1 of 1

品名:	RC4-52-42A 14(带灯全塑) 绿正负 黄负正
料号:	5242A14-8GY20010FY22 (WR50045)
型号:	RJ45
图号:	
单位:	mm
比例:	1:1
纸张:	A4