

1


2

3


4

REVISIONS



REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.06.23	阿树




Circuit diagram



P.C.B LAYOUT




MOUNTING SURFACE




DMX-XXXD-X

1:1A以下
3:3A


1:转换型 SPDT



2:常闭型 SPST-NC



3:常开型 SPST-NO




AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15

UNSPECIFIED TOLERANCES




Connection


XKB INDUSTRIAL PRECISION CO.,LIMITED




117




135




150




180




12U




16U




115G



151U



141U



000

DESIGN	阿树	VIEW:	MODEL TYPE: MICRO SWITCH
CHECKED		UNIT: mm/in	PART NO.: DM1-000D-1
APPROVED		SIZE: A4	DWG NO.: X-DM1-000D-1
			SCALE: N/A
			PAGE: 1/1
			REVISION: A1

1

2

3

4