




Part No	CKT	A	B	C
MX1.25-2PWZ-MR	2	1.25	3.20	4.30
MX1.25-3PWZ-MR	3	2.50	4.45	5.55
MX1.25-4PWZ-MR	4	3.75	5.70	6.80
MX1.25-5PWZ-MR	5	5.00	6.95	8.05
MX1.25-6PWZ-MR	6	6.25	8.20	9.30
MX1.25-7PWZ-MR	7	7.50	9.45	10.55
MX1.25-8PWZ-MR	8	8.75	10.70	11.80
MX1.25-9PWZ-MR	9	10.00	11.95	13.05
MX1.25-10PWZ-MR	10	11.25	13.20	14.30
MX1.25-11PWZ-MR	11	12.50	14.45	15.55
MX1.25-12PWZ-MR	12	13.75	15.70	16.80
MX1.25-13PWZ-MR	13	15.00	16.95	18.05
MX1.25-14PWZ-MR	14	16.25	18.20	19.30
MX1.25-15PWZ-MR	15	17.50	19.45	20.55
MX1.25-16PWZ-MR	16	18.75	20.70	21.80
MX1.25-17PWZ-MR	17	20.00	21.95	23.05
MX1.25-18PWZ-MR	18	21.25	23.20	24.30
MX1.25-19PWZ-MR	19	22.50	24.45	25.55
MX1.25-20PWZ-MR	20	23.75	25.70	26.80

适用线路板(PCB LAYOUT)

DIMA±0.1

1.25±0.05

Ø0.60±0.05

胶芯外形

技术指标(Technical Index):

- 塑件表面应光洁,无毛边,无明显收缩、缺陷、裂纹等现象。(The surface of the plastic parts should be smooth,no rough edges,no obvious shrinkage,defects,cracks and other phenomena)
- 锁扣窗口:2~3PIN为1个,≥4PIN为2个。
(Lock Configuration:2 to 3Pin is 1,≥4Pin is 2)
- 温度范围(Temperature range):-25°C~+85°C.
- 额定电压(Rated voltage):125V,AC/DC(=等效).
- 接触电阻(Contact resistance):≤0.02Ω.
- 绝缘电阻(Insulation resistance):≥100MΩ

序号	品名	材质
①	A型卧式DIP型WTB胶芯 1.25 Pitch S/T Wire To Board Housing DIP(H=3.2)	LCP UL94V-0 本色 Natural
②	A型卧式DIP型WTB端子 1.25 Pitch S/T Wire To Board Terminal DIP(H=3.2)	铜合金/表面镀锡 Copper Alloy/ Tin Plating

MANUFACTURE DWG

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS:

X.:±0.50

X.X:±0.20

X.XX:±0.10

ANGLES:

±1°

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co.,Ltd

TITLE:

1.25 Pitch A型弯针WTB

PAR MX1.25-NPWZ-MR

DWN Lucas

CHKD Ethan

APVD Jacob

SCALE:1:1 UNIT:MM

SIZE:A4

SHEET:1F1

REV:A

NOTE(注):

1.10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE $\pm 0.2\text{mm}$.(10片孔距累积公差 $\pm 0.2\text{mm}$.)

2.CARRIER CAMBER NOT TO EXCEED 1mm IN 100mm.

(载带拱/弧形MAX:1/100mm.)

3.ALL DIMENSIONS MEET EIA-481 REQUIREMENTS.

(所有的尺寸要满足协会EIA-481规范.)

4.MATERIAL: CLEAR ANTISTATIC PS.

(载带材料:透明 PS.)




5.THICKNESS: $0.40 \pm 0.05\text{mm}$. (载带厚度: $0.40 \pm 0.05\text{mm}$.)

6.PACKING LENGTH PER REEL: 10.56 METERS. (每卷包装长度: 10.56米.)



7.COMPONENT LOAD PER REEL: 850 PCS. (每卷包装数量: 850只, 前后各空包15只.)

8. 纸箱装箱以不超过装箱线为准, 空余位置用塑料泡沫及保尼龙填充.

9. 纸箱分小、中、标准型3种规格型号: 装箱为整箱(左下包装量)采用标准型纸箱包装, 未达到整箱数量以产品量适当采用小型或中型纸箱包装.



CKT (1.25mm pitch)	W	PCS/REEL	REEL/CARTON	SUM(PCS)
2	16	850	14	11900
3				
4				
5				
6				
7	24	850	10	8500
8				
9				
10				
11				
12				
13	32	850	8	6800
14				
15				
16				
17				
18	44	850	6	5100
19				
20				



纸箱型号 Carton Type	小型 Small Size	中型 Medium	标准型 Standard
高度 Height (CM)	7.5	15	32

CKT (1.25mm pitch)	B0	W	F	S
2	4.60	16	7.50	
3	5.85			
4	7.10			
5	8.35			
6	9.60			
7	10.85	24	11.50	
8	12.10			
9	13.35			
10	14.60			
11	15.85			
12	17.10			
13	18.35	32	14.2±0.10	28.45
14	19.60			
15	20.85			
16	22.10			
17	23.35			
18	25.85	44	20.2±0.15	40.45
19	28.35			
20	30.85			

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co., Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: 1.25-A型弯针WTB载带包装	
DECIMALS:	ANGLES:	PAR	MX1.25-NPWZ-MR
X.:±0.50	±2°	DWN	Lucas
X.X:±0.25		CHKD	Ethan
X.XX:±0.15		APVD	Jacob
CUSTOMER COPY		SCALE:1:1	UNIT:MM
		SIZE:A4	SHEET:1F1
			REV:A