






ROHS Compliant

MAPX	MODIFICATION	DATE	DRAW	APPROVE
合高(H)		公座单高	母座单高	
1.5		1.3	1.4	
2.0		1.3	1.9	
2.5		1.3	2.4	



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ 。

Part No	CKT	A	B	C
BTB0.524-10PLBDW3-MB42	2X5	2.00	3.40	5.50
BTB0.524-12PLBDW3-MB42	2X6	2.50	3.90	6.00
BTB0.524-14PLBDW3-MB42	2X7	3.00	4.40	6.50
BTB0.524-16PLBDW3-MB42	2X8	3.50	4.90	7.00
BTB0.524-18PLBDW3-MB42	2X9	4.00	5.40	7.50
BTB0.524-20PLBDW3-MB42	2X10	4.50	5.90	8.00
BTB0.524-22PLBDW3-MB42	2X11	5.00	6.40	8.50
BTB0.524-24PLBDW3-MB42	2X12	5.50	6.90	9.00
BTB0.524-26PLBDW3-MB42	2X13	6.00	7.40	9.50
BTB0.524-28PLBDW3-MB42	2X14	6.50	7.90	10.00
BTB0.524-30PLBDW3-MB42	2X15	7.00	8.40	10.50
BTB0.524-32PLBDW3-MB42	2X16	7.50	8.90	11.00
BTB0.524-34PLBDW3-MB42	2X17	8.00	9.40	11.50
BTB0.524-36PLBDW3-MB42	2X18	8.50	9.90	12.00
BTB0.524-38PLBDW3-MB42	2X19	9.00	10.40	12.50
BTB0.524-40PLBDW3-MB42	2X20	9.50	10.90	13.00
.....	...	...	...	...
BTB0.524-100PLBDW3-MB42	2X50	24.50	25.90	28.00

序号	品名	材质	MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd			
①	0.5 Pitch C型 单槽立式BTB母座胶芯	LCP UL94 V-0 颜色:米黄色	UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE:0.5 Pitch C型单槽立式BTB 母座业务图(单高2.4)		
②	0.5 Pitch C型 单槽立式BTB母座端子	铜合金/表面点镀金	DECIMALS:	ANGLES:		PAR	BTB0.524-XPLBDW3-MB42	
			X.:±0.50	±1°		DWN	Lucas	
			X.X:±0.20			CHKD	Ethan	
			X.XX:±0.10			APVD	Jacob	
		CUSTOMER COPY		SCALE:1:1	UNIT:MM			
				SIZE:A4	SHEET:1F1	REV:A		